SEA-LINE BRAYT S2 EXTRA SHINE HOLOGRAM REMOVER



Technical information

Product components: Polishing compound S2 – one pack product

Volume: Single pack: 500 g

Sea-Line® Brayt S2 polishing compound is a universal finishing product for all **Product description:**

types of finishing coatings. It eliminates defects after polishing and provides a

perfect mirrored shine.

It is a universal product, appropriate for every kind of gelcoat, PE and PU Recommended use:

varnishes in the furniture industry and in the manufacturing of products made

of composites.

High quality polishing minerals provide immaculate, mirrored shine without holograms, and an optimal proportion of solids and a binder enable to keep

your work area clean and makes the residual product easy to remove.

Thanks to an optimal composition, the product does not cause excessive

heating. By working with Sea-Line[®] S2 we save our time.

Cut level: Gloss level: 10 /10

Physiochemical Characteristics:

Density: 1.0 kg/l Color: Turquoise Viscosity: >7 mm²/s (40°C)

Preparing the surface: For difficult surface, product can be treated as supplement after use of Sea-

Line[®] S1 polishing compound.

Wash the work surface.

finishing sanding: P3000 < (only if it is necessary to remove scratches)

Remove dust and degrease again.

Wash the work surface other contaminations with fresh water.

Soft sponge (black), microfiber finishing pad, lambwool (Type MM Sea-Line® Method of application:

BRAYT).

Product works best when its temperature is $15 - 25^{\circ}$ C **Application conditions:**

Application: Apply Sea-Line® S2 in small quantity on the surfaces to be treated.

polishing should be performed on a small surface.

In order to remove scratches and other defects, polish with limited

polish with max 2000 RMP to reach perfect gloss.

To provide the best quality of polished surface, gradually decrease the contact force and rotations.

Further Work: After polishing, remove all residues with a microfiber cloth.

To protect the surface use:

S4 Protect wax

S5 Quick wax

July 2018 1

SEA-LINE BRAYT S2 EXTRA SHINE HOLOGRAM REMOVER



Technical information

Storage:

Storage in sealed container at 0 – 35°C



Product components should be kept in tightly sealed containers, in dry and cool spaces, far away from the sources of flames, heat, and sun rays.

Caution: After every use, containers should be closed immediately!

Expiration date: 24 months from production date.

Quality Guarantee: Production, quality control, and the realization of deliveries fulfill the demands

of ISO 9001 and 14001 standards.

All data in this document have been prepared for informational purposes. We can not take responsibility for the results of user actions over which we have no control. Responsibility of the user is to make the test sample and determine the suitability of the product for individual applications. Sea-Line do not take responsibility for any damages, or loss of profits associated with the improper use of the products.

All information is based on scrupulous laboratory research and many years of experience. Our position of market leadership does not free us from constant quality control of our products. However, we do not accept responsibility for the effects of improper use or storage of our products, or for the effects of using our products in any way contrary to the standards of good workmanship.

TROTON sp. z o.o. Ząbrowo.

July 2018 2